



ThyssenKrupp Acciai Speciali Terni S.p.A. con Unico Socio

A Company of ThyssenKrupp Stainless

**EXTRALEGA per Acciaio Inossidabile**

|                         |              |            |             |                   | <b>Mar 2010</b>  |
|-------------------------|--------------|------------|-------------|-------------------|------------------|
| Tipi di<br>Acciaio      | Marca<br>AST | AISI       | EURONORM    | SIMBOLO           | EXTRA<br>EURO/MT |
| ACCAI<br>AL<br>CR       | 409 LI       | 409        | 4512        | X2CrTi12          | <b>284</b>       |
|                         | 410 S        | 410 S      | 4000        | X6Cr13            | <b>293</b>       |
|                         | 430          | 430        | 4016        | X6Cr17            | <b>333</b>       |
|                         | 430 TI       | 430 TI     | 4510        | X3CrTi17          | <b>332</b>       |
|                         | 441 LI       | 441        | 4509        | X2CrTiNb18        | <b>412</b>       |
|                         | 439 M        | 439        | 4510        | X3CrTi17          | <b>332</b>       |
|                         | 434          | 434        | 4113        | X5CrMo17          | <b>556</b>       |
|                         | str 12       |            | 4003        | X2CrNi12          | <b>329</b>       |
|                         | 470Li        |            |             |                   | <b>384</b>       |
|                         | 460Li        |            |             |                   | <b>360</b>       |
|                         | 444          | 444        | 4521        |                   | <b>847</b>       |
| ACCAI<br>AL<br>CR - NI  | 202          |            | 4373        | X12CrMnNiN18-9-5  | <b>800</b>       |
|                         | 202Cu        |            |             |                   | <b>898</b>       |
|                         | 301          | 301        | 4310        | X10CrNi18-8       | <b>1.106</b>     |
|                         | 301 Mo       | 301        | 4310        | X10CrNi18-8       | <b>1.235</b>     |
|                         | 304          | 304        | 4301        | X5CrNi18-10       | <b>1.198</b>     |
|                         | 304PSQ       | 304        | 4301        | X5CrNi18-10       | <b>1.294</b>     |
|                         | 304 L        | 304 L      | 4306        | X2CrNi19-11       | <b>1.342</b>     |
|                         | 321          | 321        | 4541        | X6CrNiTi18-10     | <b>1.342</b>     |
|                         | 305          | 305        | 4303        | X4CrNi18-12       | <b>1.535</b>     |
|                         | 4828         |            | 4828        | X15CrNiSi20-12    | <b>1.612</b>     |
|                         | 309 S        | 309 S      | 4833        | X12CrNi23-13      | <b>1.671</b>     |
| 310 S                   | 310 S        | 4845       | X8CrNi25-21 | <b>2.360</b>      |                  |
| ACCAI<br>AL<br>CR-NI-MO | SAF 2205     | S 31803    | 4462        | X2CrNiMoN22-5-3   | <b>1.622</b>     |
|                         | 316          | 316        | 4401        | X5CrNiMo17-12-2   | <b>1.989</b>     |
|                         | 316 L        | 316 L      | 4404        | X2CrNiMo17-12-2   | <b>1.989</b>     |
|                         | 316 Ti       | 316 TI     | 4571        | X6CrNiMoTi17-12-2 | <b>1.994</b>     |
|                         | 316 SLD      | 316 Sup. L | 4435        | X2CrNiMo18-14-3   | <b>2.269</b>     |